

**Garant**
**Shrink-fit chuck with cooling channel bores, SK 50 short, Clamping range Ø D1: 14mm**

**Order data**

Order number	302292 14
GTIN	4045197288523
Item class	31A

**Description**
**Version:**

- **High-temperature steel.**
- **Size 3 -5 for carbide, from size 6 for HSS and carbide.**
- **All shanks hard turned (for smooth running!).**
- **With RFID/Balluffchip bore.**

With **coolant hole bores** tapped for plugging.

Coolant hole bores at clamping Ø D1: 3, 4 and 5 mm cannot be plugged.

**Application:**

For clamping tools with parallel shank to h6 tolerance.

Suitable for inductive, contact, and hot-air shrink units.

**Optional extras:**

Pull studs (PS) No. 308600 – 308800. PS wrenches No. 308820 – 308835, Shrink-fit chuck extensions No. 302410 – 302419. Shrink-fit units, accessories No. 354210 – 354450, balancing screws set No. 309906 size 180.

**Technical description**

Ø D <sub>2</sub>	27 mm
Clamping Ø D <sub>1</sub>	14 mm
Overhang dimension A	80 mm
External Ø D	34 mm

Cooling channel bore	lockable
Adapter	SK 50 short
Arbor standard	ISO 7388-1
Shape	ADB
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	≤ 3 µm
Machining strategy	HSC
Machining strategy	HPC
Type of product	Shrink-fit chuck

## Accessories

Shrink-fit unit Type SU1	354210 SU1
Pull studsealed suitable for steep tapers 50	308660 50
Shrink-fit chuck extension 4.5°without length adjustment screw Ø d / Ø D1 32/14 mm	302410 32/14
Shrink-fit chuck extension 4.5°with length adjustment screw Ø d / Ø D1 32/12 mm	302412 32/12
Shrink-fit chuck extension 4.5°with length adjustment screw Ø d / Ø D1 25/14 mm	302412 25/14
Pull studsealed, form B suitable for steep tapers 50	308620 50
Shrink-fit chuck extension 4.5°with length adjustment screw Ø d / Ø D1 32/14 mm	302412 32/14
Shrink fit chuck extension 3°, vibration-damped Ø d / Ø D1 25/14 mm	302417 25/14
Basic tool mountingfor SK for SK taper shank 50	354225 50
Special pull stud with internal thread suitable for steep tapers 50	308740 50
Shrink-fit chuck extension 4.5°without length adjustment screw Ø d / Ø D1 32/14 mm	302416 32/14
Pull stud 90°sealed suitable for steep tapers 50	308790 50

Pull stud 60°sealed suitable for steep tapers 50	308785 50
Shrink-fit chuck extension 4.5°with length adjustment screw Ø d / Ø D1 25/12 mm	302412 25/12
Pull stud 45°sealed suitable for steep tapers 50	308765 50
Shrink-fit chuck extension 4.5°without length adjustment screw Ø d / Ø D1 32/12 mm	302416 32/12
Wrench for pull studsISO 7388 suitable for ISO taper size 50	308830 50
Shrink-fit chuck extension 4.5°without length adjustment screw Ø d / Ø D1 25/12 mm	302410 25/12
Pull studForm A suitable for steep tapers 50	308600 50
Shrink-fit chuck extension 4.5°without length adjustment screw Ø d / Ø D1 25/14 mm	302416 25/14
Cooling adapter short4.5° for clamping Ø 12,1-16 mm	354235 12,1-16
Screening plate for coilSU1 for clamping Ø 12-20 mm	354240 12-20
Shrink-fit chuck extension 4.5°without length adjustment screw Ø d / Ø D1 25/14 mm	302410 25/14
Shrink-fit chuck extension 4.5°without length adjustment screw, with through coolant holes Ø d / Ø D1 32/14 mm	302414 32/14
Cooling unit Type CU1	354215 CU1
Pull studForm B suitable for steep tapers 50	308640 50
Pull stud 45°sealed suitable for steep tapers 50	308760 50
Pull stud 90°sealed suitable for steep tapers 50	308795 50
Cooling adapter long4.5° for clamping Ø 12,1-16 mm	354236 12,1-16
Shrink fit chuck extension 3°, vibration-damped Ø d / Ø D1 20/12 mm	302415 20/12
Special pull stud with no internal threadsealed suitable for steep tapers 50	308720 50
Pull stud, 18CrNiMo7sealed, form B suitable for steep tapers 50	308615 50
Pull studsealed, form B suitable for steep tapers 50	308650 50
Pull studsealed, form A suitable for steep tapers 50	308610 50
Pull stud, 18CrNiMo7Form A suitable for steep tapers 50	308605 50

Wrench for pull studs DIN ISO 7388-1 (formerly DIN 69872)  
suitable for ISO taper size 50

308820 50

Shrink-fit chuck extension 4.5° without length adjustment  
screw  $\varnothing d / \varnothing D1$  32/12 mm

302410 32/12

Shrink-fit chuck extension 4.5° without length adjustment  
screw  $\varnothing d / \varnothing D1$  25/12 mm

302416 25/12