

**Holder M-Drill, Shank: ZS20****Order data**

Order number	080750 ZS20
GTIN	4069515008594
Item class	BAW

Description**Version:**

Very quickly produce core holes in thin-walled materials using frictional heat. Can be used on CNC, NC and pillar drilling machines.

The M-Drill collet chucks are equipped with an aluminium cooling ring with bores to efficiently dissipate the heat generated during flow drilling. As a result, no heat is introduced into the machine spindle.

Standard or long; with or without a collar.

Suitable for:

HOLEX ER collets No. 308964.

ER clamping wrench No. 309680 25.

HOLEX fluteless tap No. 139130 or No. 139180.

Technical description

Spare ER clamping nut	25
Overhang dimension A	76 mm
ER chuck key	25

Data sheet

External Ø D	42 mm
for ER collets	25
Clamping range	1 - 16 mm
Type of product	Collet chucks