

SICOMET
omniFIT

Nut lock, 50 ml, Manufacturer's designation: 100M



Order data

Order number	083307 100M
GTIN	4058093008997
Item class	08G

Description

Version:

The use of thread-lockers prevents the screw fastenings from accidentally releasing and coming undone. The single-component anaerobic adhesives are suitable for all thread types and forms. Screw fastenings are sealed. Seizing is reliably prevented.

Thread locking fluid.

Application:

Low strength – can be undone with normal tools.

Medium strength – can still be undone with normal tools.

High strength – Can be undone only with special tools or by heating (>150 °C). Universal anaerobic thread locking, medium viscosity, for metals.

Note:

Before applying locking fluid, clean the threads with general-purpose cleaner No. 083391 and No. 083392. Quick and easy handling for 50 ml bottles with No. 083344 size 50.

Technical description

for thread size M to	M36
minimum break-away torque	17 - 30 Nm

Manufacturer's designation	100M
Labelling of hazardous substances	GHS05: Corrosive
Labelling of hazardous substances	GHS07 caution
Colour	red
Capacity	50 ml
Suitable for application area	Thread locking
Suitable for material	Metal
Operating temperature range	-60 - 140 °C
Maximum gap size	0.1 mm
Chemical basis	Dimethacrylate
Storage temperature	8 - 21 °C
Functional strength to	3 h
Dynamic viscosity	700 - 1000 mPas
Disassembly	with normal tool
Strength class	medium strength
Density	1.07 g/cm ³
Product name attribute	50 ml
Type of product	Thread lock

Accessories

Peristaltic hand pump with metering needle set Suitable for container size 50 ml

083344 50