



Electrical angle grinder CG, M14 grinding spindle thread, for 125 mm discs Ø, with restart inhibit, with anti-vibration handle



Order data

Order number	077111 7222936
GTIN	4014586901503
Item class	03F

Description

Version:

FEIN – Compact angle grinder Ø 125 mm.

- **Robust, powerful motor for everyday use.**
- **High level of protection for the user thanks to recoil monitoring, restart inhibit and anti-vibration handle.**
- **High overload capability thanks to direct motor cooling; grinding head can be rotated in 90° steps (optimum switch position for the application).**
- **Grinding media can be changed quickly without the need for tools thanks to the quick-release clamping nut.**

Supplied with:

Handle, safety guard, clamping nut, wrench.

Technical description

Manufacturer's designation	CG10-125
Restart block	yes

Data sheet

Special features	short body
Power consumption	1000 W
maximum vibration to EN	8.5 m/s ²
maximum cutting depth	35 mm
AC supply voltage	230 V
Weight	2.1 kg
maximum disc Ø	125 mm
Mains frequency	50 Hz
maximum speed	11000 min ⁻¹
Type of product	Angle grinder