

Garant**Master Mute boring bar A.. SCLCR 95°, for indexable inserts CC.., right****Order data**

Order number	265008 10/06
GTIN	4069515024433
Item class	29E

Description**Version:**

Round shank without clamping face. Carbide-reinforced shank.

Note:

Boring bar can be shortened as far as length L_{min} . Use **only with internal cooling** (temperature resistance of up to max. 100°C).

Technical description

ISO code toolholder	A10X SCLCR/L06
Set of insert screws	269028 38
Insert size	6 mm
Overhang L_1	110 mm
Setting angle κ	95 degrees
Shank $\varnothing D_s$	10 mm
Centre offset L_3	6.1 mm
Standard	Works standard
Series	Master Mute
suitable indexable insert	CC.. 0602..
Overall length L	161 mm
Minimum pre-drill $\varnothing D_{min}$	12 mm
Connection thread	M9×0.5

Data sheet

Application type	right-hand
Shank type	Steel
Vibration	damped
Through-coolant	yes
Application	Internal longitudinal turning
Application	Facing
Type of product	Boring Bar

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/265008-10/06>