

**Wedge block, highest support height: 60mm****Order data**

Order number	374905 60
GTIN	4069515012096
Item class	32H

Description**Version:**

Very rigid design; spheroidal graphite cast iron and hardened steel. **The ground wedge surfaces provide for precision and even height adjustment** with an accuracy better than 0.1mm. Either the knurled screw or a hexagon socket wrench can be used for height adjustment. The double action results in a long stroke and precise vertical movement without lateral displacement.

Application:

Particularly for working with heavy cast or forged parts on large machine tools after marking-out.

Supplied with:

Interchangeable ball jack pad No. 375000.

Note:

Flat component support face with centring hole Ø 12 mm for jack pads No. 375000 – 375030.

Technical description

lowest support height	47 mm
Height adjustment per spindle rotation	9 mm
Load capacity	28 kN

Data sheet

Type	6460
Footprint length	63 mm
Footprint width	54 mm
highest support height	60 mm
Type of product	Wedge