

Garant**Master Mute boring bar A.. SCLCL 95°, for indexable inserts CC.., left****Order data**

Order number	265009 16/06
GTIN	4069515024549
Item class	29E

Description**Version:**

Round shank without clamping face.

Note:

Boring bar can be shortened as far as length L_{min} . Use **only with internal cooling** (temperature resistance of up to max. 100°C).

Technical description

Set of insert screws	269028 38
ISO code toolholder	A16X SCLCR/L06
Insert size	6 mm
suitable indexable insert	CC.. 0602..
Shank $\varnothing D_s$	16 mm
Standard	Works standard
Minimum pre-drill $\varnothing D_{min}$	20 mm
Series	Master Mute
Setting angle κ	95 degrees
Overhang L_1	96 mm
Overall length L	158 mm
Centre offset L_3	11 mm
L_{min}	96 mm

Data sheet

Connection thread	G1/4
Application type	left-hand
Shank type	Steel
Vibration	damped
Through-coolant	yes
Application	Internal longitudinal turning
Application	Facing
Type of product	Boring Bar

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/265009-16/06>