

**Wedge block, highest support height: 105mm****Order data**

Order number	374905 105
GTIN	4069515012119
Item class	32H

Description**Version:**

Very rigid design; spheroidal graphite cast iron and hardened steel. **The ground wedge surfaces provide for precision and even height adjustment** with an accuracy better than 0.1mm. Either the knurled screw or a hexagon socket wrench can be used for height adjustment. The double action results in a long stroke and precise vertical movement without lateral displacement.

Application:

Particularly for working with heavy cast or forged parts on large machine tools after marking-out.

Supplied with:

Interchangeable ball jack pad No. 375000.

Note:

Flat component support face with centring hole Ø 12 mm for jack pads No. 375000 – 375030.

Technical description

highest support height	105 mm
Load capacity	70 kN
Footprint length	118 mm

Data sheet

lowest support height	80 mm
Footprint width	87 mm
Height adjustment per spindle rotation	1.2 mm
Type	6460
Type of product	Wedge