

**Wedge block, highest support height: 155mm****Order data**

|              |               |
|--------------|---------------|
| Order number | 374905 155    |
| GTIN         | 4069515012126 |
| Item class   | 32H           |

**Description****Version:**

Very rigid design; spheroidal graphite cast iron and hardened steel. **The ground wedge surfaces provide for precision and even height adjustment** with an accuracy better than 0.1mm. Either the knurled screw or a hexagon socket wrench can be used for height adjustment. The double action results in a long stroke and precise vertical movement without lateral displacement.

**Application:**

**Particularly for working with heavy cast or forged parts on large machine tools after marking-out.**

**Supplied with:**

**Interchangeable ball jack pad No. 375000.**

**Note:**

Flat component support face with centring hole Ø 12 mm for jack pads No. 375000 – 375030.

**Technical description**

|                                        |        |
|----------------------------------------|--------|
| lowest support height                  | 135 mm |
| Load capacity                          | 175 kN |
| Height adjustment per spindle rotation | 2 mm   |

## Data sheet

|                        |        |
|------------------------|--------|
| highest support height | 155 mm |
| Type                   | 6460   |
| Footprint width        | 125 mm |
| Footprint length       | 140 mm |
| Type of product        | Wedge  |