

**Self-levelling cross-hair laser GLL, Type: GLL20****Order data**

Order number	468490 GLL20
GTIN	4053423303315
Item class	46T

Description**Version:**

Green cross-hairs for optimum visibility even under poor lighting conditions. Thanks to the rubber-reinforced housing and IP65 protection class, the lasers are durable and suitable for robust use on construction sites. Convenient, quick and secure attachment thanks to the LB 10 professional universal holder with very strong magnets. Dual power supply enables seamless switching between Li-ion rechargeable battery and alkaline batteries, eliminating downtime. One horizontal and 2 vertical 360° lines permit a wide range of new applications for simultaneous marking, alignment and levelling indoors. Large working range up to 120 m using the LR 7 Professional receiver (accessories).

Function:

IP65: Protected against jets of water from all directions and protected against penetration by dust (dust-tight), also completely protected against touching.

Supplied with:

4x battery No. 081561 size LR6, LB 10 universal holder, laser target plate, bag.

Technical description

Threaded socket for stand	1/4 in
---------------------------	--------

Data sheet

Levelling range	±4 degrees
Range	20 m
Weight	560 g
Colour of the laser	green
Power supply	Battery-powered
Series	GLL
Laser class	2
Length	129 mm
Error limit	±0.3 mm/m
#Number of batteries contained	4
IP Index of Protection	IP 65
#Article no of the battery / rechargeable battery fitted	081561 LR6
Width	68 mm
Height	116 mm
Type of product	Cross laser

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/468490-GLL20>