



Torque wrench without plug-in head, maximum torque: 200N·m



Order data

Order number	656220 200
GTIN	4013288219787
Item class	63F

Description

Version:

Very sturdy single-handed torque wrench (square drive 1/2 inch) with ergonomic 2-component handle and reversible ratchet with 45 teeth. Easy adjustment and locking of the specified value is ensured as the user can hear and feel the tool engage when the scale value is reached and easily read off the reading on the main scale and fine scale. User can clearly hear and feel the trigger mechanism upon reaching the set torque value. For right-handed use. **Units of measure: Nm, lbfft.**

Function:

The wrench triggers giving a "signal" (clearly audible acoustic tone and noticeable vibration) and afterwards is immediately ready for use again.

Standard:

Tested to DIN EN ISO 6789.

Accuracy:

Percentage of the displayed value **only for right-hand tightening: ±3 %.**

Cutting dataa:

Legend for drawing and formula:

l_1 = Lever length without plug-in head

l_2 = Adjusted reference dimension on the torque wrench

l_3 = Lever length including factory calibration reference dimension

l_4 = Reference dimension of the plug-in head

L = Total length of the tool

T_1 = Torque to be set

T_2 = Specified torque

Technical description

Trigger principle	mechanical short travel release
-------------------	---------------------------------

Data sheet

Standard	DIN EN ISO 6789
Measurement process	Torque
Adjustable trigger value	adjustable
Release signalling	acoustic
Release signalling	haptic
Overall length L	487 mm
Lever length including factory calibration reference dimension [I ₃]	435 mm
Weight	1264 g
Lever length without plug-in head [I ₁]	409.5 mm
maximum torque	200 Nm
Feedback	acoustic signal
Torque range	40 - 200 Nm
Calibration	O1
Measurement technology	mechanical
Connection format	for plug-in heads (rectangular socket)
Torque measuring accuracy	±3 %
Scale graduation, 1 graduation =	1 Nm
Socket for plug-in head	14×18 mm
Setting the trigger value	with adjustment scale
Display	analogue
Direction of tightening	Right-hand tightening
Test certificate	Manufacturer's test certificate
Reversible reading	Nm
Reversible reading	lbfft
Adjusted reference dimension on the torque wrench [I ₂]	25.5 mm
Exchangeable tool	Plug-in head
Deflection function	no
Slipper function	no
Quick release/ quick-change function	no

Memory pointer	no
Type of product	Torque wrenches

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/656220-200>