

AEG**Jigsaw, Type: STEP100X**

Order data

Order number	078213 STEP100X
GTIN	4002395136513
Item class	07A

Description

Version:

Sturdy general-purpose jigsaws with metal gearbox casings and overload protection.
700 W jigsaw with variable speed preselection and tool-free saw blade change.

· Connection for dust removal system.

With **FIXTEC quick-release clamping system** allows blades to be changed in seconds without any tools, and **selectable orbital stroke** for optimum cutting power and dust extraction combined with reduced saw blade wear.

Supplied with:

Supplied with chip break guard.

Supplied with 2 × saw blades, extraction adapter, sole plate, mains cable 4 m, carrying case.

Note:

For jigsaw blades see No. 588400 – 588551.

Technical description

Format	D-shape handle
maximum sawn thickness wood	100 mm
Mains frequency	50 Hz

Data sheet

Weight	2.3 kg
Nominal voltage	230 V
Orbital stroke	4-fold
Special features	general purpose use
maximum vibration to EN	10,5 m/s ²
Manufacturer's designation	STEP100X
Rate of strokes	1000 - 3200 min ⁻¹
Power consumption	700 W
Power supply	Mains-powered
maximum sawn thickness steel	10 mm
tool change without tools	yes, FIXTEC system
Type of product	Saw