


**KOMET UniTurn® turning toolholder for stationary use (without boring bar),  
Shank Ø d / Bore Ø d1: 12/8mm****Order data**

Order number	240100 12/8
GTIN	4047109019348
Item class	24S

**Description****Application:**

For turning and internal grooving on the lathe.

**Technical description**

Clamping height b	11 mm
Length a	8 mm
Shank Ø d	12 mm
Overall length L <sub>tot</sub>	70 mm
Length l <sub>2</sub>	45 mm
Bore Ø d <sub>1</sub>	8 mm
Through-coolant	yes
Type of product	Cutter holder