

Garant**GARANT Steel solid carbide milling cutter HPC, TiAlN, Ø f8 DC: 14mm****Order data**

Order number	203057 14
GTIN	4069515028493
Item class	11Z

Description**Version:**

For **roughing and finishing**. For use in unstable machining processes and for machining complex components.

Up to 1.5xD into solid material **at very high feed rates** with smooth cutting action.

Advantage:

Optimised flute form, eccentric relief ground, wide chip space.

Note:

Successor product to No. 203041.

Technical description

Feed f_z for side milling in steel $< 900 \text{ N/mm}^2$	0.1 mm
Corner chamfer angle	45 degrees
Helix angle	38 degrees
Feed f_z for slot milling in steel $< 900 \text{ N/mm}^2$	0.08 mm
Shank	DIN 6535 HB
Recess Ø D_1	13.8 mm
Tolerance nominal Ø	e8
Flute length L_c	26 mm
No. of teeth Z	4
Cutting edge Ø D_c	14 mm
Corner chamfer width at 45°	0.28 mm

Data sheet

Overall length L	83 mm
Direction of infeed	horizontal, oblique and vertical
Overhang length L ₁ incl. recess	36 mm
Shank Ø D _s	14 mm
Series	Master Steel
Coating	TiAlN
Tool material	Solid carbide
Standard	DIN 6527
Type	N
Helix angle characteristic	unequal spacing
Spacing of the cutters	unequal spacing
Cutting width a _e for milling operation	Full slot cutting depth 1×D
Cutting width a _e for milling operation	0.3×D for side milling
Through-coolant	no
Machining strategy	HPC
Colour ring	green
Type of product	End / face mill

User data

	Suitability	V _c	ISO code
Steel < 500 N/mm ²	suitable	250 m/min	P
Steel < 750 N/mm ²	suitable	200 m/min	P
Steel < 900 N/mm ²	suitable	180 m/min	P
Steel < 1100 N/mm ²	suitable	160 m/min	P
INOX < 900 N/mm ²	suitable	70 m/min	M
INOX > 900 N/mm ²	suitable	50 m/min	M
GG(G)	suitable	120 m/min	K
Uni	suitable		
wet maximum	suitable		

wet minimum	suitable only under restricted conditions
dry	suitable
Air	suitable