

Garant
Boring bar carbide, left-hand, Shank \varnothing / insert size: 16/09mm


Order data

Order number	260017 16/09
GTIN	4045197651914
Item class	21T

Technical description

Insert size	9 mm
ISO code toolholder	E16R SCLCR/L09
Centre offset L_3	10 mm
Head length L_1	16 mm
Minimum pre-drill $\varnothing D_{\min}$	18 mm
Pack of insert screws	269028 8
suitable indexable insert	CC.. 09T3..
Overall length L	200 mm
Clamping height L_2	15.5 mm
Setting angle κ	95 degrees
Shank $\varnothing D_s$	16 mm
Standard	DIN 8024
Application type	left-hand
Boring depth up to	8xD
Tool material	Carbide
Through-coolant	yes
Application	Internal longitudinal turning

Type of product	Boring bar
-----------------	------------

Accessories

Set of insert screws Type 8	269028 8
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500