

Garant
QuickTurn clamp toolholder, left-hand, Shank / insert size: 20/15mm

Order data

Order number	250607 20/15
GTIN	4045197650429
Item class	21U

Description
Advantage:

Inserts can be changed without using tools. **Release the stop at the push of a button – change the insert – press the clamp to secure it.**

A simple and convenient way to reduce non-productive times.

Consistent clamping force, high interchange accuracy, maintenance-free.

Through-coolant: no

ISO code toolholder: DDJNR/L 2025K15

suitable indexable insert: DN.. 1506..

Functional width L₄: 32 mm

Head length L₁: 46 mm

Overall length L: 125 mm

Shim: 259031 29

Technical description

Shank size	20 mm
ISO code toolholder	DDJNR/L 2025K15
Insert size	15 mm
Head length L ₁	46 mm
Functional width L ₄	32 mm
Shim screw	259025 4
Clamp	259038 7

suitable indexable insert	DN.. 1506..
Shim	259031 29
Overall length L	125 mm
Series	QuickTurn
Application type	left-hand
Standard	DIN ISO 5610
Through-coolant	no
Setting angle κ	93 °
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Clamping claw	259351
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659906 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15
Shim screw Type 4	259025 4
Shim screw	259171
Clamping claw Type 6	259038 6
Shim Type 29	259031 29
Clamping claw Type 7	259038 7
Clamping claw	259350
Shim	259271