



## Diamond burnishing tips, Tip radius: 0,2mm



### Order data

Order number

291410 0,2

GTIN

Item class

29M

### Description

#### Advantage:

Thanks to indexing there are 8 possibilities for using the diamond burnishing tips.  
Surface quality  $R_z < 1 \mu\text{m}$  possible.

#### Application:

For machining materials up to 65 HRC. Ideal for machining the surfaces of complex, continuous contours.

#### Accuracy:

Surface quality  $R_z < 1 \mu\text{m}$  possible.

#### Note:

Use the largest possible radius.

For detailed application recommendations please see the instruction handbook supplied.

### Technical description

Type of product

Smooth rolling tool