

Garant
Lever lock toolholder, left-hand, Shank / insert size: 20/15mm

Order data

Order number	250611 20/15
GTIN	4045197650566
Item class	21T

Technical description

Shim	259031 28
ISO code toolholder	PDJNR/L 2020K15
suitable indexable insert	DN.. 1506..
Head length L ₁	35 mm
Shim pins pack	259044 2
Lever	259015 8
Functional width L ₄	25 mm
Lever screw	259018 7
Shim punches pack	259047 2
Insert size	15 mm
Shank size	20 mm
Overall length L	125 mm
Series	QuickTurn
Standard	DIN ISO 5610
Application type	left-hand
Through-coolant	no

Setting angle κ	93 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Shim Type 28	259031 28
PrecisionBit for hexagon, 1/4 inch E 6.3 Hexagon 3 mm	674242 3
Lever Type 8	259015 8
Shim punches set 10 pieces Type 2	259047 2
Set of shim pins 10 pieces Type 2	259044 2
Lever screw Type 7	259018 7
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500