



Indexable insert for turning TNMG 160404, for medium machining



Order data

Order number	251582 PR115S
GTIN	4960664035779
Item class	25E

Technical description

Feed f	0.09 - 0.3 mm/rev.
Cutting depth a_p	0.5 - 2 mm
Cutting conditions	slightly interrupted
Tool material	Carbide
Number of changes/inserts	6
Main application	S
ISO code indexable insert	TNMG 160404
Cutting speed v_c main application	25 - 70 m/min
Corner radius	0.4 mm
Chip breaker	MU
Type	PR115S
Finishing/roughing assignment	Finishing

Type of product

Indexable insert for turning