

Garant**Indexable insert for turning DNMG 110408, for medium machining****Order data**

Order number	250754 HB7035-2
GTIN	4069515017022
Item class	21G

Technical description

Feed f	0.2 - 0.5 mm/rev.
ISO code indexable insert	DNMG 110408
Type	HB7035-2
Tolerance	M
Cutting depth a_p	0.3 - 4 mm
Cutting conditions	heavily interrupted
Finishing/roughing assignment	Finishing
Corner radius	0.8 mm
Number of changes/inserts	4
Tool material	Carbide
Cutting speed v_c main application	120 - 320 m/min

Data sheet

Main application	P
Chip breaker	SM
Type of product	Indexable insert for turning