

Garant**Indexable insert for turning CNMG 160612, for medium machining****Order data**

Order number	250170 HB7020-2
GTIN	4069515016124
Item class	21G

Technical description

Cutting speed v_c main application	130 - 370 m/min
Corner radius	1.2 mm
Cutting conditions	slightly interrupted
Chip breaker	SM
Finishing/roughing assignment	Finishing
Type	HB7020-2
Main application	P
Tool material	Carbide
ISO code indexable insert	CNMG 160612
Cutting depth a_p	0.3 - 4 mm
Number of changes/inserts	4

Data sheet

Feed f	0.2 - 0.5 mm/rev.
Tolerance	M
Type of product	Indexable insert for turning