

Garant
Clamp toolholder, left-hand, Shank / insert size: 32/15mm

Order data

Order number	250609 32/15
GTIN	4045197654601
Item class	21T

Technical description

ISO code toolholder	DDJNR/L 3232 P15
Shim screw	259025 10
suitable indexable insert	DN.. 1506..
Functional width L ₄	40 mm
Shank size	32 mm
Head length L ₁	40 mm
Clamp, screw, spring	259035 2
Shim	259031 28
Insert size	15 mm
Overall length L	170 mm
Series	QuickTurn
Standard	Works standard
Application type	left-hand
Through-coolant	no
Setting angle κ	93 degrees
Application	External longitudinal turning

Application	External longitudinal turning
Type of product	Boring bar

Accessories

Shim Type 28	259031 28
Shim screw Type 10	259025 10
Clamp unit Type 2	259035 2
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX20	674248 TX20
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500