

Garant**Indexable insert for turning WNMG 080408, for finish machining****Order data**

Order number	251964 HB7035-2
GTIN	4069515018623
Item class	21G

Technical description

Cutting speed v_c main application	150 - 350 m/min
Main application	P
Cutting depth a_p	0.3 - 2 mm
ISO code indexable insert	WNMG 080408
Cutting conditions	heavily interrupted
Chip breaker	SS
Corner radius	0.8 mm
Type	HB7035-2
Feed f	0.1 - 0.4 mm/rev.
Number of changes/inserts	6
Finishing/roughing assignment	Finishing
Tool material	Carbide

Type of product

Indexable insert for turning