

Garant**Indexable insert for turning VNMG 160408, for medium machining****Order data**

| | |
|--------------|-----------------|
| Order number | 251804 HB7020-2 |
| GTIN | 4069515018302 |
| Item class | 21G |

Technical description

| | |
|--------------------------------------|----------------------|
| Cutting speed v_c main application | 130 - 370 m/min |
| Cutting conditions | slightly interrupted |
| Finishing/roughing assignment | Finishing |
| Feed f | 0.2 - 0.5 mm/rev. |
| Type | HB7020-2 |
| Corner radius | 0.8 mm |
| Cutting depth a_p | 0.3 - 4 mm |
| Tolerance | M |
| ISO code indexable insert | VNMG 160408 |
| Main application | P |
| Tool material | Carbide |

Data sheet

| | |
|---------------------------|------------------------------|
| Number of changes/inserts | 4 |
| Chip breaker | SM |
| Type of product | Indexable insert for turning |