

Garant**Indexable insert for turning VC.T 160402, for finish machining****Order data**

Order number	261370 HB7010-2
GTIN	4069515022392
Item class	21G

Technical description

Cutting conditions	continuous
Tool material	Carbide
Corner radius	0.2 mm
Tolerance	M
Finishing/roughing assignment	Finishing
Main application	P
Cutting depth a_p	0.2 - 1.5 mm
Chip breaker	SS
ISO code indexable insert	VCMT 160402
Cutting speed v_c main application	150 - 500 m/min
Number of changes/inserts	2

Data sheet

Feed f	0.07 - 0.25 mm/rev.
Type	HB7010-2
Type of product	Indexable insert for turning