

**Indexable insert for turning TCMT 16T304, for finish machining****Order data**

Order number	260956 HB7010-2
GTIN	4069515021432
Item class	21G

Technical description

Main application	P
Type	HB7010-2
ISO code indexable insert	TCMT 16T304
Cutting speed v_c main application	150 - 500 m/min
Number of changes/inserts	3
Tool material	Carbide
Cutting depth a_p	0.2 - 1.5 mm
Feed f	0.07 - 0.25 mm/rev.
Finishing/roughing assignment	Finishing
Cutting conditions	continuous
Chip breaker	SS
Corner radius	0.4 mm

Type of product

Indexable insert for turning