

Garant**Indexable insert for turning VC.T 160408, for finish machining****Order data**

Order number	261374 HB7035-2
GTIN	4069515022552
Item class	21G

Technical description

Chip breaker	SS
Cutting conditions	heavily interrupted
Type	HB7035-2
Cutting depth a_p	0.2 - 1.5 mm
Tolerance	M
Cutting speed v_c main application	120 - 350 m/min
Tool material	Carbide
Finishing/roughing assignment	Finishing
Main application	P
ISO code indexable insert	VCMT 160408
Feed f	0.07 - 0.25 mm/rev.

Data sheet

Corner radius	0.8 mm
Number of changes/inserts	2
Type of product	Indexable insert for turning