

Garant**Indexable insert for turning DNMG 150608, for roughing machining****Order data**

Order number	250862 HB7020-2
GTIN	4069515017244
Item class	21G

Technical description

Main application	P
Corner radius	0.8 mm
Cutting depth a_p	1.5 - 6 mm
Cutting speed v_c main application	110 - 360 m/min
Cutting conditions	slightly interrupted
Type	HB7020-2
Tool material	Carbide
ISO code indexable insert	DNMG 150608
Chip breaker	SG
Finishing/roughing assignment	Finishing
Number of changes/inserts	4

Data sheet

Feed f	0.25 - 0.6 mm/rev.
Type of product	Indexable insert for turning