

Garant**Indexable insert for turning VNMG 160408, for medium machining****Order data**

Order number	251804 HB7035-2
GTIN	4069515018326
Item class	21G

Technical description

Feed f	0.2 - 0.5 mm/rev.
Number of changes/inserts	4
Cutting speed v_c main application	120 - 320 m/min
Cutting depth a_p	0.3 - 4 mm
Finishing/roughing assignment	Finishing
Tolerance	M
Corner radius	0.8 mm
Main application	P
Tool material	Carbide
Cutting conditions	heavily interrupted
Chip breaker	SM

Data sheet

Type	HB7035-1
ISO code indexable insert	VNMG 160408
Type of product	Indexable insert for turning