

**Indexable insert for turning SNMG 120408, for finish machining****Order data**

Order number	251144 HB7035-2
GTIN	4069515017527
Item class	21G

Technical description

Chip breaker	SS
Tool material	Carbide
Cutting depth a_p	0.3 - 2 mm
Feed f	0.1 - 0.4 mm/rev.
Cutting conditions	heavily interrupted
Main application	P
Number of changes/inserts	8
Corner radius	0.8 mm
Cutting speed v_c main application	150 - 350 m/min
ISO code indexable insert	SNMG 120408
Type	HB7035-2

Data sheet

Finishing/roughing assignment

Finishing

Type of product

Indexable insert for turning