

Garant**Master Mute exchangeable cutting head, left-hand, for CN.. indexable inserts****Order data**

Order number	265101 40/12
GTIN	4069515031745
Item class	29E

Description**Suitable for:**

Vibration-damping boring bar shanks No. 265060 – 265076.

Technical description

Screw for clamping claw	259021 8
suitable indexable insert	CN.. 1204..
Minimum pre-drill $\varnothing D_{\min}$	50 mm
Series	Master Mute
Centre offset L_3	27 mm
Overall length L	33 mm
Clamp	259038 21
Insert size	12 mm
Shim	269005 22

Shim screw	269013 9
Shank Ø D _s	40 mm
Number of coolant channels	3
Application type	left-hand
Through-coolant	yes
Type of product	Cutting head

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/265101-40/12>