

Garant**Indexable insert for turning DNMG 150604, for medium machining****Order data**

Order number	250760 HB7035-2
GTIN	4069515017084
Item class	21G

Technical description

Cutting conditions	heavily interrupted
Chip breaker	SM
Tool material	Carbide
Cutting speed v_c main application	120 - 320 m/min
Number of changes/inserts	4
Cutting depth a_p	0.3 - 4 mm
Tolerance	M
Main application	P
Corner radius	0.4 mm
Finishing/roughing assignment	Finishing
Type	HB7035-2

Data sheet

ISO code indexable insert	DNMG 150604
Feed f	0.2 - 0.5 mm/rev.
Type of product	Indexable insert for turning