

Garant**Indexable insert for turning DC.T 11T304, for finish machining****Order data**

Order number	260359 HB7020-2
GTIN	4069515020343
Item class	21G

Technical description

Feed f	0.07 - 0.25 mm/rev.
ISO code indexable insert	DCMT 11T304
Corner radius	0.4 mm
Cutting depth a_p	0.2 - 1.5 mm
Tool material	Carbide
Cutting speed v_c main application	140 - 400 m/min
Main application	P
Tolerance	M
Number of changes/inserts	2
Cutting conditions	slightly interrupted
Chip breaker	SS

Data sheet

Finishing/roughing assignment	Finishing
Type	HB7020-2
Type of product	Indexable insert for turning