



### , impact wrench, cordless impact wrench



#### Order data

Order number	074801 IDS18V200T
GTIN	4053423301106
Item class	03B

#### Description

##### Version:

Industrial impact wrench with constant, pre-selectable output torque.

- **9 levels of specific tightening torque with # +/-15% consistency to each bolt.**
- **Tightening indicator light.**
- **Durable Hall sensor switch:** Switching cycle is maximised for 2-5 times longer life compared to traditional products.
- **Differentiation of the torque (switch-off torque, max. torque, release torque).**
- **Process reliability:** Locking function for torque setting via NFC connectivity (with Pro360) to ensure process reliability.
- **Connectivity enabled for Process Control (OK/NOK recording, screw counting function).**
- **Ease of use:** Status LED on completed tightening, acoustic signal.
- **Operating comfort:** Narrow handle optimised for industrial use (without soft grip).
- **Standardised battery platform for EXACT Clutch Tools from Bosch.**
- **Increased service life and reduced noise pollution thanks to automatic switch-off.**
- **Possibility of mounting suspension hooks.**
- **Target group:** Automotive, heavy machinery, railway.

##### Note:

See No. 073851 – No. 073866 for suitable batteries and chargers.

**Technical description**

Weight	1.2 kg
maximum vibration to EN	11.6 m/s <sup>2</sup>
Type of rechargeable battery	Lithium-ion
Manufacturer's designation	IDS 18V-200 T
No load speed	0 - 2500 min <sup>-1</sup>
Battery voltage	18 V
Number of rechargeable batteries contained	0
Power supply	Battery-powered
typical application	Heavy Duty
Number of impacts	0 - 3500 min <sup>-1</sup>
Tool arbor size	1/2 in
maximum torque	300 Nm
Tool arbor drive profile	External square drive
Type of product	Impact wrench