

Garant**Mini burr GARANT Master Uni – medium, Carbide, Type: AF0324****Order data**

Order number	546906 AF0324
GTIN	4069515032070
Item class	51D

Description**Version:**

Carbide mini burr with shank Ø 3 mm. With guide face at the tip. Precise deburring without damage to the workpiece.

Application:

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

Technical description

Series	Master Uni
Shape description	Cylindrical with guide face
Head length	24 mm
Head Ø	3 mm
Shank Ø	3 mm
Overall length	40 mm
Tool material	Carbide
Long shank	no
Type of product	Burr

User data

	Suitability	V _c	ISO code
--	-------------	----------------	----------

Alu Mg	suitable only under restricted conditions
Steel < 900 N/mm ²	suitable
Steel < 1400 N/mm ²	suitable
Steel < 55 HRC	suitable
Steel < 60 HRC	suitable
INOX	suitable
Ti	suitable
GG(G)	suitable
Uni	suitable