

Garant**Indexable insert for turning VBMT 160402, for finish machining****Order data**

Order number	261150 HB7035-2
GTIN	4069515021951
Item class	21G

Technical description

Finishing/roughing assignment	Finishing
Feed f	0.07 - 0.25 mm/rev.
Cutting depth a_p	0.2 - 1.5 mm
Type	HB7035-2
Corner radius	0.2 mm
Cutting speed v_c main application	120 - 350 m/min
Chip breaker	SS
Tool material	Carbide
Main application	P
Number of changes/inserts	2
ISO code indexable insert	VBMT 160402

Data sheet

Cutting conditions

heavily interrupted

Type of product

Indexable insert for turning