

**Indexable insert for turning DC.T 11T308, for finish machining****Order data**

Order number	260361 HB7010-2
GTIN	4069515020381
Item class	21G

Technical description

Cutting speed v_c main application	150 - 500 m/min
Cutting conditions	continuous
Tolerance	M
Main application	P
Corner radius	0.8 mm
Chip breaker	SS
ISO code indexable insert	DCMT 11T308
Cutting depth a_p	0.2 - 1.5 mm
Feed f	0.07 - 0.25 mm/rev.
Tool material	Carbide
Number of changes/inserts	2

Data sheet

Finishing/roughing assignment	Finishing
Type	HB7010-2
Type of product	Indexable insert for turning