


**Indexable insert for turning WNMG 080404, for medium machining****Order data**

Order number	252068 HB7035-2
GTIN	4069515018845
Item class	21G

Technical description

Cutting conditions	heavily interrupted
Feed f	0.2 - 0.5 mm/rev.
Main application	P
Cutting depth a_p	0.3 - 4 mm
Tool material	Carbide
Corner radius	0.4 mm
Finishing/roughing assignment	Finishing
Number of changes/inserts	6
Chip breaker	SM
Type	HB7035-2
Tolerance	M
ISO code indexable insert	WNMG 080404

Data sheet

Cutting speed v_c main application

120 - 320 m/min

Type of product

Indexable insert for turning