

Garant**Indexable insert for turning DNMG 150608, for medium machining****Order data**

Order number	250762 HB7035-2
GTIN	4069515017145
Item class	21G

Technical description

Tolerance	M
Corner radius	0.8 mm
Feed f	0.2 - 0.5 mm/rev.
Number of changes/inserts	4
Finishing/roughing assignment	Finishing
Type	HB7035-2
Chip breaker	SM
Cutting conditions	heavily interrupted
Cutting speed v_c main application	120 - 320 m/min
Cutting depth a_p	0.3 - 4 mm
ISO code indexable insert	DNMG 150608

Data sheet

Tool material	Carbide
Main application	P
Type of product	Indexable insert for turning