

Garant**Indexable insert for turning VC.T 160408, for medium machining****Order data**

Order number	261459 HB7020-2
GTIN	4069515022705
Item class	21G

Technical description

Cutting depth a_p	0.3 - 2 mm
Type	HB7020-2
Cutting conditions	slightly interrupted
Corner radius	0.8 mm
Number of changes/inserts	2
Chip breaker	SM
Tool material	Carbide
Feed f	0.08 - 0.3 mm/rev.
Main application	P
ISO code indexable insert	VCMT 160408
Cutting speed v_c main application	110 - 350 m/min

Data sheet

Finishing/roughing assignment	Finishing
Tolerance	M
Type of product	Indexable insert for turning