

Garant**GARANT Uni Hero solid carbide drill, plain shank DIN 6535 HB, TiAlSiN, Ø DC h7: 3,3mm****Order data**

Order number	123021 3,3
GTIN	4069515034357
Item class	13M

Description**Version:**

The ultimate in universality and profitability in one tool. **Robust tool design** and **convex-concave curved cutting edge design** for optimum tool stability and chip breakage in a wide range of materials. **Special chip chamber geometry** and **polished chip chambers** for ideal chip evacuation and maximum process reliability. **Ultra-smooth TiAlSiN high-performance coating** to effectively reduce wear and the formation of built-up edges.

Note:

Flute length $L_c = L_2 + 1.5 \times D_c$.

Technical description

Standard	Manufacturer's standard
Feed f in steel $< 1100 \text{ N/mm}^2$	0.08 mm/rev.
Flute length L_c	34 mm
Tolerance nominal $\varnothing$	h7
Nominal $\varnothing D_c$	3.3 mm
recommended maximum drilling depth L_2	29.1 mm
Shank $\varnothing D_s$	6 mm
Overall length L	72 mm
Number of cutting edges Z	2
Series	Uni

Data sheet

Coating	TiAlSiN
Tool material	Solid carbide
Version	4xD
Point angle	140 degrees
Shank	DIN 6535 HB to h6
Through-coolant	yes, with 25 bar
Machining strategy	HPC
Semi-Standard	yes
Colour ring	orange
Type of product	Mono jobber drills

User data

	Suitability	V _c	ISO code
Alu plastics	suitable only under restricted conditions	140 m/min	N
Aluminium (short chipping)	suitable	150 m/min	N
Steel < 500 N/mm ²	suitable	120 m/min	P
Steel < 750 N/mm ²	suitable	115 m/min	P
Steel < 900 N/mm ²	suitable	110 m/min	P
Steel < 1100 N/mm ²	suitable	80 m/min	P
Steel < 1400 N/mm ²	suitable	70 m/min	P
INOX < 900 N/mm ²	suitable	65 m/min	M
INOX > 900 N/mm ²	suitable	60 m/min	M
Ti > 850 N/mm ²	suitable	35 m/min	S
GG(G)	suitable	95 m/min	K
Uni	suitable		
wet maximum	suitable		
wet minimum	suitable		

Air

suitable only under
restricted conditions