


**Indexable insert for turning TNMG 160408, for medium machining****Order data**

Order number	251544 HB7020-2
GTIN	4069515018043
Item class	21G

Technical description

Type	HB7020-2
Number of changes/inserts	6
Chip breaker	SM
Corner radius	0.8 mm
ISO code indexable insert	TNMG 160408
Finishing/roughing assignment	Finishing
Cutting depth a_p	0.3 - 4 mm
Cutting speed v_c main application	130 - 370 m/min
Tolerance	M
Tool material	Carbide
Feed f	0.2 - 0.5 mm/rev.
Cutting conditions	slightly interrupted

Main application	P
Type of product	Indexable insert for turning