

Garant**Indexable insert for turning KNUX 160410L, for medium machining****Order data**

Order number	251038 HB7020-2
GTIN	4069515017404
Item class	21G

Technical description

Cutting conditions	slightly interrupted
Feed f	0.2 - 0.5 mm/rev.
Type	HB7020-2
Number of changes/inserts	2
Finishing/roughing assignment	Finishing
Chip breaker	SM
Tool material	Carbide
Chip diverter	2.2 mm
Cutting depth a_p	0.3 - 4 mm
Cutting speed v_c main application	130 - 370 m/min
Main application	P
ISO code indexable insert	KNUX 160410L
Type of product	Indexable insert for turning