

**Indexable insert for turning DC.T 11T308, for finish machining****Order data**

Order number	260361 HB7020-2
GTIN	4069515020404
Item class	21G

Technical description

Type	HB7020-2
ISO code indexable insert	DCMT 11T308
Corner radius	0.8 mm
Cutting conditions	slightly interrupted
Tool material	Carbide
Finishing/roughing assignment	Finishing
Tolerance	M
Feed f	0.07 - 0.25 mm/rev.
Number of changes/inserts	2
Cutting speed v_c main application	140 - 400 m/min
Main application	P

Data sheet

Cutting depth a_p	0.2 - 1.5 mm
Chip breaker	SS
Type of product	Indexable insert for turning