

**Garant****Master Mute exchangeable cutting head, left-hand, for TC.. indexable inserts****Order data**

|              |               |
|--------------|---------------|
| Order number | 265223 20/11  |
| GTIN         | 4069515035705 |
| Item class   | 29E           |

**Description****Suitable for:**

Vibration-damping boring bar shanks No. 265060 – 265076.

**Technical description**

|                                          |             |
|------------------------------------------|-------------|
| Minimum pre-drill $\varnothing D_{\min}$ | 25 mm       |
| Overall length L                         | 20 mm       |
| Insert size                              | 11 mm       |
| Centre offset $L_3$                      | 13 mm       |
| Series                                   | Master Mute |
| suitable indexable insert                | TC.. 1103.. |
| Insert screw                             | 269028 47   |
| Shank $\varnothing D_s$                  | 20 mm       |
| Number of coolant channels               | 2           |

|                  |              |
|------------------|--------------|
| Application type | left-hand    |
| Through-coolant  | yes          |
| Type of product  | Cutting head |

### **Suitable products**

<https://www.hoffmann-group.com/GB/en/hom/p/265223-20/11>