

**Indexable insert for turning TC.T 16T304, for medium machining****Order data**

Order number	260986 HB7010-2
GTIN	4069515021678
Item class	21G

Technical description

Cutting conditions	continuous
Cutting depth a_p	0.3 - 2 mm
Type	HB7010-2
Tolerance	M
Main application	P
Feed f	0.08 - 0.3 mm/rev.
Cutting speed v_c main application	120 - 440 m/min
ISO code indexable insert	TCMT 16T304
Chip breaker	SM
Corner radius	0.4 mm
Finishing/roughing assignment	Finishing
Tool material	Carbide

Data sheet

Number of changes/inserts	3
Type of product	Indexable insert for turning