

**Garant****Master Mute exchangeable cutting head, left-hand, for TC.. indexable inserts****Order data**

|              |               |
|--------------|---------------|
| Order number | 265223 40/16  |
| GTIN         | 4069515035736 |
| Item class   | 29E           |

**Description****Suitable for:**

Vibration-damping boring bar shanks No. 265060 – 265076.

**Technical description**

|                                      |             |
|--------------------------------------|-------------|
| Insert size                          | 16 mm       |
| Overall length L                     | 32 mm       |
| Centre offset L <sub>3</sub>         | 27 mm       |
| Insert screw                         | 269028 50   |
| Minimum pre-drill Ø D <sub>min</sub> | 50 mm       |
| Shim                                 | 269005 19   |
| Series                               | Master Mute |
| Shim screw                           | 269013 8    |
| suitable indexable insert            | TC.. 16T3.. |

## Data sheet

|                            |              |
|----------------------------|--------------|
| Shank Ø D <sub>s</sub>     | 40 mm        |
| Number of coolant channels | 3            |
| Application type           | left-hand    |
| Through-coolant            | yes          |
| Type of product            | Cutting head |

### Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/265223-40/16>