

Garant**Indexable insert for turning VC.T 160408, for medium machining****Order data**

Order number	261459 HB7035-2
GTIN	4069515022729
Item class	21G

Technical description

Finishing/roughing assignment	Finishing
Corner radius	0.8 mm
Cutting speed v_c main application	80 - 290 m/min
ISO code indexable insert	VCMT 160408
Tolerance	M
Cutting depth a_p	0.3 - 2 mm
Feed f	0.08 - 0.3 mm/rev.
Chip breaker	SM
Number of changes/inserts	2
Type	HB7035-2
Cutting conditions	heavily interrupted

Data sheet

Main application	P
Tool material	Carbide
Type of product	Indexable insert for turning