

**Garant****Master Mute exchangeable cutting head, right-hand, for VC.. indexable inserts****Order data**

|              |               |
|--------------|---------------|
| Order number | 265226 40/16  |
| GTIN         | 4069515035781 |
| Item class   | 29E           |

**Description****Suitable for:**

Vibration-damping boring bar shanks No. 265060 – 265076.

**Technical description**

|                                          |             |
|------------------------------------------|-------------|
| Overall length L                         | 28 mm       |
| Series                                   | Master Mute |
| Minimum pre-drill $\varnothing D_{\min}$ | 50 mm       |
| Shim                                     | 269005 24   |
| Centre offset $L_3$                      | 27 mm       |
| Shim screw                               | 269013 8    |
| Insert screw                             | 269028 50   |
| suitable indexable insert                | VC.. 1604.. |

## Data sheet

|                            |              |
|----------------------------|--------------|
| Insert size                | 16 mm        |
| Shank Ø D <sub>s</sub>     | 40 mm        |
| Number of coolant channels | 3            |
| Application type           | right-hand   |
| Through-coolant            | yes          |
| Type of product            | Cutting head |

### Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/265226-40/16>