

Garant**Master Mute boring bar A.. SVJCR 142°, for indexable inserts VC.., right****Order data**

Order number	265038 12/07
GTIN	4069515036252
Item class	29E

Description**Version:**

Carbide-reinforced round shank without clamping face.

Note:

Use **only with internal cooling** (temperature resistance of up to max. 100°C).

Technical description

Overall length L	189 mm
Set of insert screws	269028 53
Setting angle κ	142 degrees
Minimum pre-drill $\varnothing D_{\min}$	14 mm
Centre offset L_3	7 mm
Standard	Works standard
Overhang L_1	132 mm
Series	Master Mute
ISO code toolholder	A12X SVJCR/L07
Insert size	7 mm
Shank $\varnothing D_s$	12 mm
suitable indexable insert	VC.. 0702..
Application type	right-hand
Shank type	Steel

Data sheet

Vibration	damped
Through-coolant	yes
Application	Internal longitudinal turning
Application	Facing
Type of product	Boring Bar

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/265038-12/07>